



HELAGO-CZ, s.r.o.  
Commercial Register maintained by the Regional Court in Hradec Králové  
Section C, File 17879  
Kladská 1082  
500 03 Hradec Králové 3  
Company ID: 25 96 39 61, VAT: CZ 25963961  
Phone: 495 220 229, 495 220 394  
Fax: 495 220 154  
GSM gate: 602 123 096  
E-mail: [info@helago-cz.cz](mailto:info@helago-cz.cz)  
Web: <http://www.helago-cz.cz>

B-510FL Trinocular Fluorescence Microscope  
Order code: **0501.B510FL**



Cena bez DPH

6.240,00 Eur

Price with VAT

7.550,40 Eur

#### Parameters

Microscopes types	Laboratory
Serie	B-510
Number of eyepieces	Trinocular
Number of lenses	4
Zoom of lenses	4x, 10x, 20x, 40x
Illumination	LED
Quantitative unit	ks

- Detailed description

**Observation Methods:** Brightfield, Fluorescence

**Head:** Trinocular, 30° inclined, rotatable 360°, ±5 dioptic adjustment on left eyepiece, interpupillary adjustment 50 – 75 mm, 3 positions photo port: 0/100, 50/50, 100/0 ratios

**Eyepieces:** Plan wide field, PL 10x/22, high eyepoint

**Nosepiece:** Quintuple revolving nosepiece, rotation on ball bearings

**Objectives:** IOS W-PLAN F 4x, 10x, 20x, 40x

**Stage:** Double layer with mechanical sliding stage, size 233 x 147 mm, X-Y movement range 78 x 54 mm. Belt-drive in X direction. Vernier scale on two axes, accuracy 0.1 mm

**Condenser:** Swing-out type condenser, sliding-in, N.A. 0.2/0.9, with centering system

**Focusing:** Coaxial coarse and fine focusing mechanism (graduated, 0.002 mm) with upper stop. Adjustable tension of coarse focusing knob.

#### Fluorochromes:

- 4 positions slider, with 2 included filter sets:
- Fluorescence B: EX 460-490, DM 505, EM 515LP: Acridine Yellow, Acridine Orange, Auramine, DiO, DTAF, FITC, GFP, YFP, etc.
- Fluorescence G: EX 510-550, DM 570, EM 590LP: DiI; Blu Evans, Feulgen, Rhodamine, Texas Red, TRITC, PI, etc.

**Transmitted Illumination & Diaphragms:** High-efficiency X-LED3 (3.6 W), manual brightness control. Köhler illumination system with field diaphragm

#### Epi-fluorescence:

- HBO 100 W high pressure mercury bulb
- Bulb average lifetime: approx. 300 h.
- Input voltage: 100/240 Vac, 50/60 Hz.
- Max. required power: 130 W

Do you want to print the page now?

Hide some parts of page before printing



Print partially

Print the page as you see it now



Print complete page

(this box will not be printed)

Edit before printing

Hover your mouse over some part of page, a red rectangle will appear. Click it to hide the selected content of page.



Print!



Show hidden